

KBSW200811 SLAMWARE Web Portal Function Overview 2

Slamwareweb portal

- [Dashboard](#)
 - [Device Info](#)
- [System](#)
 - [Firmware Update](#)
 - [Networking](#)
 - [Basic](#)
 - [Advanced](#)
 - [Lidar](#)
 - [Restart](#)
 - [Change Password](#)
- [Advanced](#)
 - [Debug Access](#)

Dashboard

Device Info

1.Device Information

2.Networking StatusSSIDIP

1).AP

SLAMWARE CoreWiFi2.4GWiFi5GWiFiWiFDHCP192.168.11.1AP5GSLAMWARE core

2).Station

SLAMWARE CoreWiFiWiFISLAMWARE CoreHigh Speed BusIP

3.ComponentsCP0LIDARBASEMCU

←

→

↺

🏠

🔍

192.168.11.1/index.html#/dashboard/info

📖

☆

🔖

🔍

🔗

⋮

Management

Dashboard

Device Info

System

Advanced

Device Information

Product Name: Slamtec Slamware Core E1M1

Firmware Version: release-2.7.4-rc1-sdp-E1M1-20200717

Device Model: E1M1

Networking Status

Wireless Mode: AP(5G)

Wireless SSID: SLAMWARE-D2295B

Wireless IP: 192.168.11.1

Components


Type	SN	Firmware Version	Comments
CP0	A4EE20F3E1EEF79AD5E7F4F924435030	2.64	
LIDAR	B2D28FC1E8839EF2C0E69EF76A652405	1.20	Model: A2M8
BASE	05DEFF333133555251255324	1.20	00FF:DD11

System

SystemDevice InfoSign inSystemadminadmin111



Microsoft EdgeGoogle Chromeweb portal




Firmware Update

Select FileStart Firmware UpdateDevice Info

10



support@slamtec.com




Networking

BasicAdvanced

Basic

- 1.AP
- 2.APWIFI SSIDWiFiSLAMWARE-XXXXXX
- 3.Disabled>Apply Network settings



4.APStationSTA>WiFiWiFi

Advanced

1.

Network Settings

Internet Access

Ethernet

WiFi

Not Connected To Internet

2./

3.DHCPStatic AssignedDHCP Server

Ethernet Settings - Ethernet

Enabled

Network Mode

DHCP

Static Assigned

DHCP Server

IP Address

192.168.12.13

Netmask

255.255.255.0

Gateway

DNS Server

4./

5.AP

6.APWiFi SSIDWiFi

7.APSTA

8.STADHCPStatic Assigned

WiFi Settings

Work Mode

AP

STA

Disabled

Connect to...

Network Mode

DHCP

Static Assigned

Apply Network Settings

Wireless Status

 AdvancedApply Network Settings

Lidar

Model

SN

Health

Firmware Version

Supported Scan ModesCommentsTypicalUse this mode

←

→

↺

🏠

🔍 192.168.11.1/index.html#/system/lidar

📖

☆

⚙️

🔍

🔗

⋮

Management

Dashboard

System

Firmware Update

Networking

Lidar

Restart

Change Password

Advanced

admin

General

Model: A2M8

SN: B2D28FC1E8839EF2C0E69EF76A652405

Health: Healthy

Firmware Version: 1.20

Supported Scan Modes

Id	Name	Samples Per Second	Max Distance	Comments	Operations
0	Standard	2008.0321285140562	16		Use this mode
1	Express	4016.0642570281125	16	Typical	Use this mode

Slamtec

Copyright © 2019 Shanghai Slamtec Co., Ltd.

Restart

←

→

↺

🏠

🔍 192.168.11.1/index.html#/system/restart

📖

☆

⚙️

🔍

🔗

⋮

Management

Dashboard

System

Firmware Update

Networking

Lidar

Restart

Change Password

Advanced

admin

Restart Device

☒ Soft Restart

Soft restarting device will only restart some major processes in the system. It is much faster than hard restarts.

☐ Hard Restart

Hard restarting device will reboot the whole software system. It is slower than soft restarts, but providing a cleaner software environment.

Restart

Change Password



192.168.11.1/index.html#/system/change_password

Management

- Dashboard
- System
 - Firmware Update
 - Networking
 - Lidar
 - Restart
 - Change Password**
 - Advanced

Change Password

Old Password New Password

Please input your old password! Please input your new password!

Advanced

Debug Access

/

192.168.11.1/index.html#/advanced/debug_access

Management

- Dashboard
- System
- Advanced
 - Debug Access**

Debug Access

Debug access is a feature for Slamtec employees only

Challenge Code: A4EE20F3E1EEF79AD5E7F4F924435030

Response Code